

## MOCK X2 TRAINING DEVICE Fact Sheet



**Description:**

The Mock x2 Training Device is designed for use with simulators and other target systems to train operators without expending live TASER rounds.



Smart Firearms Training Devices, Inc  
232 S. Mulberry, Suite 102  
Mesa, AZ 85202  
sales@smartfirearms.us  
www.smartfirearms.us

**Construction:**

High impact ABS with subcomponents constructed of acetal delrin and steel.

**Lasers:**

- 4 lasers total
- 2 IR targeting lasers and 2 RED aiming lasers
- IR lasers are Class1A 780nm with the option to use 850nm or 980nm
- RED aiming lasers are 650nm and are currently Class 3R which can be replaced with Class 1 lasers that are programable for any pulse length for different simulator applications

**Batteries:**

2 AA batteries with an expected life of approximately 22 weeks of normal use.

Electronics: 1 main circuit board with an ATMEL 328P processor and 2 daughter circuit boards controlling ARC functions.

**Audio:**

An internal speaker provides audio for startup/power on, dart shots fired, and ARC audio when side ARC buttons are depressed.

**Safety Select Lever (Left and Right):**

On and off functionality. Each trigger pull deploys two darts (laser shots). After second pull, 4 darts, weapon is empty. You reset the simulated weapon by toggling the safety selector off then back on.

**Rear User Indication Display Screen:**

Screen displays shot count.

**Future growth:**

Capacity will allow the cartridge to be changed out.



Smart Firearms Training Devices, Inc  
232 S. Mulberry, Suite 102  
Mesa, AZ 85202  
sales@smartfirearms.us  
www.smartfirearms.us